# **DPF Catalyst Cleaner**

**DPF / Catalyst Cleaner Autoprofiline** 

## **Product properties**

The DPF/Catalyst Cleaner dissolves and removes all contamination and soot residues from the particulate filter and the catalyst – no disassembling required. The product eliminates any performance decrease or disruption caused by contaminated particulate filter and catalysts. DPF/Catalyst Cleaner restores the complete function of the diesel particulate filter and catalyst.

The product is also ideal for EGR-valve cleaning.

- Dissolves and removes contamination in the diesel particulate filter and catalyst.
- Cleaning without dismantling
- Evaporates residue-free

### Area of application

Cleaning of the diesel particulate filter and catalyst.

### Application

#### Attention: The motor must be in hot operating condition. Shake the can well before use! (Approx. 1 min)

Dismantle the temperature, pressure sensor or access port on the DPF / catalyst and insert the probe through the opening. Spray the cleaner with the probe inserted into the particulate filter/catalyst in 5-second intervals until the DPF / catalyst is proper filled with the foam. Close the opening after application. When the cleaner has been applied the deposits are released and dispersed in the particulate filter/catalyst. During the normal drive operation the micro-fine dirt particles combust. Restart the regeneration process through a workshop tester. Finally remove the faulty memory entry or delete existing errors. Afterwards perform a test drive consisting of about 20 minutes.

DPF/Catalyst Cleaner is usable for all closed particulate filter systems. Check the oil level before cleaning. Oil change is necessary if oil dilution is performed with diesel.

For an optimized regeneration we recommend to add the DPF Clean (43241) into the fuel tank after doing the test drive. For petrol engines we recommend OXICAT (43243).

### Consumption

Sufficient for one application / diesel particulate filter / catalyst.

### **Technical data**

Physical state: aerosol Colour: clear/colourless Odour: characteristic pH-Value (at 68 °F): 11,4 Initial boiling point and boiling range: 100 °C Flashpoint: 75 °C Lower explosion limit: 1,1 Vol.-% Upper explosion limit: 14,0 Vol.-% Ignition temperature: 270 °C Vapour pressure (at 68 °F): 8000 hPa Density at 68 °F: 1,011 g/cm

Available size	Item no.	PU
400ml	43159	12



Our information is based on careful examination and may be considered as reliable. Hower, all information supplied is a non-binding advise. No liability for printing errors, technical modifications and errors excepted.

07338 Leutenberg Germany

Tel.: +49 (0)36734 230-0 Fax: +49 (0)36734 230-22